

03

**Model :**

**SMOOTH  
250**



## MONOPOLAR MODE

### CUT

MODE	POWER	LOAD	OPERATING FREQ
PURE	250 W	500Ω	480 Khz
BLEND 1	200 W	500Ω	480 Khz
BLEND 2	150 W	500Ω	480 Khz
BLEND 3	150 W	500Ω	480 Khz

### COAG

MODE	POWER	LOAD	OPERATING FREQ
SPRAY	80 W	500Ω	480 Khz
FULGURATE	100W	500Ω	480 Khz
DESICCATE	100W	500Ω	480 Khz

### BIPOLAR

MODE	POWER	LOAD	OPERATING FREQ
SOFT	70 W	300Ω	480 khz
FORCE	70 W	300Ω	480 khz

glamaticpharma.com



## Standard Accessories



CHUCK HANDLE  
WITH **ELECTRODES**



BIPOLAR FORCEP  
WITH **CABLE**



SILICON PATIENT  
PLATE WITH **CORD**



MONOPOLAR / BIPOLAR  
FOOT SWITCH



DISPOSABLE HAND  
SWITCH PENCIL

